




Cytoflex 30




Fluorochrome	%Max	Ex	Em	Filters	BV421	BV510	BV605	BV711	BV786
1 BV421	54.8	<input type="checkbox"/>	<input type="checkbox"/>	450/40	40.8%	6.2%	2.4%	1.9%	5.8%
2 BV510	72.3	<input type="checkbox"/>	<input checked="" type="checkbox"/>	525/40	1.9%	34.3%	0.2%	0.3%	0.5%
3 BV605	59.2	<input type="checkbox"/>	<input type="checkbox"/>	610/20	x	4.2%	26.5%	x	x
4 BV711	61.9	<input type="checkbox"/>	<input checked="" type="checkbox"/>	712/25	x	x	4.3%	35.1%	0.2%
5 BV786	59.5	<input type="checkbox"/>	<input type="checkbox"/>	780/60	x	1.5%	11.8%	0.6%	x



Fluorochrome	%Max	Ex	Em	Filters	BV421	BV510	BV605	BV711	BV786
1 BV421	98.2	<input type="checkbox"/>	<input checked="" type="checkbox"/>	450/45	47.5%	7.3%	2.8%	2.1%	6.6%
2 BV510	100.0	<input type="checkbox"/>	<input type="checkbox"/>	525/40	1.9%	34.3%	0.2%	0.3%	0.5%
3 BV605	99.1	<input type="checkbox"/>	<input checked="" type="checkbox"/>	610/20	x	4.2%	26.5%	x	x
4 BV711	100.0	<input type="checkbox"/>	<input type="checkbox"/>	712/25	x	x	4.3%	35.1%	0.2%
5 BV786	99.0	<input type="checkbox"/>	<input checked="" type="checkbox"/>	780/60	x	x	x	22.1%	61.3%



Fluorochrome	%Max	Ex	Em	Filters	FITC	PE	PE-CF...	PE-Cy...	PE-Cy7
1 FITC	88.0	<input type="checkbox"/>	<input checked="" type="checkbox"/>	525/40	62.9%	0.4%	0.1%	x	1.8%
2 PE	61.6	<input type="checkbox"/>	<input checked="" type="checkbox"/>	585/42	12.5%	70.4%	26.0%	5.0%	16.4%
3 PE-CF594	55.2	<input type="checkbox"/>	<input checked="" type="checkbox"/>	610/20	2.3%	12.6%	40.8%	0.9%	3.3%
4 PE-Cy5.5	76.9	<input type="checkbox"/>	<input checked="" type="checkbox"/>	690/50	x	2.8%	8.7%	42.1%	2.0%



Fluorochrome	%Max	Ex	Em	Filters	APC	APC-R...	APC-H7
1 APC	77.1	<input type="checkbox"/>	<input checked="" type="checkbox"/>	660/20	40.2%	3.4%	7.5%
2 APC-R700	80.0	<input type="checkbox"/>	<input checked="" type="checkbox"/>	712/25	10.1%	42.6%	1.7%
3 APC-H7	38.2	<input type="checkbox"/>	<input checked="" type="checkbox"/>	780/60	x	8.9%	64.5%